







	Name	Current lineup	Difficulty	Load Flask	Output Speeds	Minimum Vacuum	Bore	Trap Requirement	Resolution	General Usage
	SPD-1 Legacy	Current production model. Stocked inventory item. Ships next day.	Easy Novice	2 liter	500-1000ml per hr Low rate with hose. Fast rate with laminar.	E2M28/30 or E2M28/30 + Volatiles pump	Thermometer: 14/20 Inlet: 24/40 Discharge: 24/40	#24 Monocow->CT-1 Basic(2L) #24 Laminar Path->CT-1 #34(2L) #24 Valve LP->CT-1 #34(2L)	Med-High	The most basic legacy system offered. Easy operation, forgiving with mistakes. Can be used with any distillation.
	SPD-2 FC34	Current production model. Stocked inventory item. Ships next day.	Easy Novice	2 liter 5 liter	500-2000ml per hr Low rate with hose. Fast rate with laminar.	E2M28/30 or E2M28/30 + Volatiles pump	Thermometer: 24/40 Inlet: 34/45 Discharge: 29/42	#29 Monocow->CT-1 Basic(2-5L) #29 Laminar Path->CT-1 #34(2-5L) #29 Valve LP->CT-1 #34(2-5L)	Med-High	The most basic fraction collecting system offered. This is a smaller head that solved higher volume/output with novice users. Easy operation, forgiving with mistakes. Can be used with any distillation.
	SPD-5 FC45	Current production model. Limited stock / special order. Ships when available.	Easy Skilled novice	5 liter 12 liter 22 liter	1000-3000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5L - E2M28/30 + Volatiles pump 12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Thermometer: 24/40 Inlet: 45/50 Discharge: 29/42	#29 Laminar->One CT-1 INV CUP(2-5L) #29 Laminar->Dual CT-1 INV CUP(5-22L) #29 Valve LP->Dual CT-1 INV CUP(5-22L)	Med-High	This system offers the fastest/highest potency distillation with clarity unmatched in the industry. This is the third series that inovated distillation with the fraction collector technology. Streamlined operation, requires skilled user. Should be used with greener/gummier material of poor or questionable crude.
	SPD-5.3 FC45 Shorty	Current production model. Stocked inventory item. Ships next day.	Easy Skilled moderate	5 liter 12 liter 22 liter	1000-3000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5L - E2M28/30 + Volatiles pump 12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Thermometer: 24/40 Inlet: 45/50 Discharge: 29/42	#29 Laminar->One CT-1 INV CUP(2-5L) #29 Laminar->Dual CT-1 INV CUP(5-22L) #29 Valve LP->Dual CT-1 INV CUP(5-22L)	Med-High	This system offers the fastest/highest potency distillation with clarity unmatched in the industry. This is the third series that inovated distillation with the fraction collector technology. Streamlined operation, requires skilled user. Should be used with medium-good crude.
	SPD-5.4 FC45 Nano	Current production model. Stocked inventory item. Ships next day.	Easy Skilled moderate	5 liter 12 liter 22 liter	1000-3000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5L - E2M28/30 + Volatiles pump 12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Thermometer: 24/40 Inlet: 45/50 Discharge: 29/42	#29 Laminar->One CT-1 INV CUP(2-5L) #29 Laminar->Dual CT-1 INV CUP(5-22L) #29 Valve LP->Dual CT-1 INV CUP(5-22L)	Low-Med-High	This system offers the fastest/highest potency distillation with clarity unmatched in the industry. This is the third series that inovated distillation with the fraction collector technology. Streamlined operation, requires skilled user. Should be used with good-great crude.
	SPD-6 FC55	Current production model. Limited stock / special order. Ships when available.	Easy Skilled novice	5 liter 12 liter 22 liter	1000-4000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5L - E2M28/30 + Volatiles pump 12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Thermometer: 34/45 Inlet: 55/50 Discharge: 34/45	#34 Laminar->Dual CT-1 INV CUP(5-22L) #34 Valve LP->Dual CT-1 INV CUP(5-22L)	Med-High	This system offers the fastest/highest potency distillation with clarity unmatched in the industry. This is the fourth series that inovated distillation with the fraction collector technology. Streamlined operation, requires skilled user. Should be used with greener/gummier material of poor or questionable crude.
	SPD-6.3 FC55 Shorty	Current production model. Stocked inventory item. Ships next day.	Easy Skilled moderate	5 liter 12 liter 22 liter	1000-4000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5L - E2M28/30 + Volatiles pump 12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Thermometer: 34/45 Inlet: 55/50 Discharge: 34/45	#34 Laminar->Dual CT-1 INV CUP(5-22L) #34 Valve LP->Dual CT-1 INV CUP(5-22L)	Med-High	This system offers the fastest/highest potency distillation with clarity unmatched in the industry. This is the fourth series that inovated distillation with the fraction collector technology. Streamlined operation, requires skilled user. Should be used with medium-good crude.
	SPD-6.4 FC55 Nano	Current production model. Stocked inventory item. Ships next day.	Easy Skilled moderate	5 liter 12 liter 22 liter	1000-4000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5L - E2M28/30 + Volatiles pump 12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Thermometer: 34/45 Inlet: 55/50 Discharge: 34/45	#34 Laminar->Dual CT-1 INV CUP(5-22L) #34 Valve LP->Dual CT-1 INV CUP(5-22L)	Low-Med-High	This system offers the fastest/highest potency distillation with clarity unmatched in the industry. This is the fourth series that inovated distillation with the fraction collector technology. Streamlined operation, requires skilled user. Should be used with good-great crude.
	SPD-4 MPD Modified Path Distillation Bertha	Current production model. Stocked inventory item. Limited stock / special order. Ships when available.	Medium Skilled expert	5 liter 12 liter 22 liter	1000-6000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5/12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Flange Inlet: 100mm Flange O-Ring 100mm Discharge: 34/45	#34 Laminar->Dual CT-1 INV CUP(5-22L) #34 Valve LP->Dual CT-1 INV CUP(5-22L)	Med-High-Fine	This system offers first of its kind multi-pathway distillation chamber technology. Dual vapor fractionation pathways with a built in key. Suggested use with less sensitive compounds. This is the series where the fraction collector was first used on high speed flange heads. Advanced operation, requires expert knowledge. Should be used with poor-medium-good-great crude, remediate as needed.
	SPD-4 MPD Modified Path Distillation HB-1	Current production model. Stocked inventory item. Limited stock / special order. Ships when available.	Medium Skilled expert	5 liter 12 liter 22 liter	1000-6000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5/12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Flange Inlet: 100mm Flange O-Ring 100mm Discharge: 34/45	#34 Laminar->Dual CT-1 INV CUP(5-22L) #34 Valve LP->Dual CT-1 INV CUP(5-22L)	High-Fine	This system mirrors our multi-pathway distillation chamber technology. Reverse ball vapor bump trap pathway with a removable key, rejection shelf and fraction collector. Suggested use with all compounds. This is the 6L per hour head that broke the existing Summit record with Breakingdabs (user dev). Advanced operation, requires expert knowledge. Should be used with poor-medium-good-great crude, remediate as needed.
	SPD-4 MPD Modified Path Distillation HB-2	Current production model. Stocked inventory item. Limited stock / special order. Ships when available.	Medium Skilled expert	5 liter 12 liter 22 liter	1000-6000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5/12/22L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Flange Inlet: 100mm Flange O-Ring 100mm Discharge: 34/45	#34 Laminar->Dual CT-1 INV CUP(5-22L) #34 Valve LP->Dual CT-1 INV CUP(5-22L)	High-Fine	This system offers extremely high speeds and high refinement at ultra low vacuum >1u. The 'donut bore' & 'no-vig' pathway with fraction collector offer excellent distillations/clarity. Suggested use with all compounds. This is the 6L per hour head that broke the existing Summit record with Breakingdabs (user dev). Advanced operation, requires expert knowledge. Should be used with poor-medium-good-great crude, remediate as needed.
	SPD-7 USPD Ultra Short Path Distillation	Current production model. Stocked inventory item. Limited stock / special order. Ships when available.	Medium Skilled jedi level	22 liter	1000-10,000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	22L - Diffusion pump array	Thermo (Flask Vapor): 24/40 Inlet: 55/50 Discharge: 29/42 LamTrap In: 55/50 LamTrap Exit: 34/45 Vacuum Guage Port: 24/40	Assembly->Dual CT-1 INV CUP(22L)	Med-High-Fine	This is the most advanced shortpath. All users are vetted prior to purchase. You must have advanced distillation knowledge. Ultra low vacuum pumps required. High accuracy gauges required. This is the lowest temp head available on the market, and the fastest head ever produced. Expert user development with WholeFarm.
	SPD-7.1 USPD Ultra Short Path Distillation Micro	Current production model. Stocked inventory item. Limited stock / special order. Ships when available.	Difficult Skilled expert	5 liter	1000-5000ml per hr Low rate with hose. Fast rate with laminar. will exceed rates with apollo sweep.	5L - Dual E2M28/30 + Volatiles pump or Diffusion pump array	Thermo (Flask Vapor): 24/40 Inlet: 45/50 Discharge: 29/42 LamTrap In: 45/50 LamTrap Exit: 34/45 Vacuum Guage Port: 24/40	Assembly->One CT-1 INV CUP(5L) Assembly->Dual CT-1 INV CUP(5L)	Med-High-Fine	This is the most advanced shortpath. All users are vetted prior to purchase. You must have advanced distillation knowledge. Ultra low vacuum pumps required. High accuracy gauges required. This is the lowest temp head available on the market, and the fastest head ever produced. Expert user development with WholeFarm.